


02/2024

Good morning!



Flashing and vibrating alarm clocks – wake up to the method you prefer: By flashes of light, vibration or loud tones.

HUMANTECHNIK – your partner
for audiological products





»Who wears his hearing aids at night? Not me. And a flashing light will wake me on time – reliably.«



»Clearly visible: your ringing alarm clock

Good morning! Wake up on time and by the method you prefer. Then it's bound to be a good morning – and a nice day.



Should you be interested in the ideal combination between your alarm clock and your Humantechnik alerting system, please ask your specialist dealer for corresponding information brochures.

Choose how you want to be woken

The HUMANTECHNIK portfolio features convenient flashing and vibrating alarm clocks and offers various methods for your choice: Alarm sound, flashing light or vibration.

Do you own a HUMAN-TECHNIK alerting system?

The Humantechnik portfolio also includes alarm clocks with receivers for wireless alerting systems. These will also display a ring at

the door, an incoming phone call, a person calling, act as a baby-phone, will wake you if the fire alarm has been set off and will also forward other alerts.

On the road?

You need not miss out on efficient awakening when travelling. The compact alarm clocks »VC-10« or »travelTim« accompany you with precise time-giving and a reliable waking service – and they also fit into small luggage.



Flashing and vibrating alarm clocks with inbuilt receiver for Humantechnik alerting systems display the source of alerts through coloured LEDs and inform you with bright lights.

DS-2: digital alarm clock



»Up to date. The DS-2 is a perfect match: Elegantly designed, versatile and convenient – just as I like it.«

DS-2: The latest generation of digital alarm clocks sets standards in design, function and convenience.

The impressively elegant design of the »DS-2« contains intelligent digital technology, which offers a wide choice of waking methods. A strong sound generator and the amazingly powerful LED strip are included by default. Furthermore, the »DS-2« offers a connection for additional alerting modules, for example a vibrating pad.

Independent flashing alarm clock or special receiver alarm clock for HUMANTECHNIK alerting systems

The »DS-2« is available in 3 versions: As an independent flashing alarm clock or as a wireless receiver alarm clock for either the alerting systems »lisa RF« or »lisa-signolux« with all according functions.

Digital alarm clock DS-2

black	Item no.: A-3114-0
white	Item no.: A-3114-W

»lisa-signolux« receiver alarm clock

with built wireless »lisa-signolux« receiver and event indication

black	Item no.: A-2634-0
white	Item no.: A-2634-W

Digital alarm clock

»lisa DS-2/RF«

with built wireless »lisa RF« receiver and event indication

black	Item no.: A-3252-0
-------	--------------------



Specifications

Dimensions (HxWxD):	123x210x63
Weight:	408 g
Power supply unit:	12 V / 1A
Lead of power supply:	1,8 m

DS-2: Main features at a glance:

- ◆ Large and clearly distinguishable illuminated digits for displaying time and alarm setting (can be deactivated on the versions »lisa-signolux« receiver alarm clock and »lisa DS-2/RF«)
- ◆ Unmistakable loud alarm tone, adjustable in volume and pitch (can be deactivated)
- ◆ Visual alarm through a powerful LED strip (can be deactivated)
- ◆ Snooze function
- ◆ Automatic adjustment of display brightness
- ◆ Selectable 12/24 hours display mode
- ◆ Power-cut backup
- ◆ Connection socket for vibrating pad and vibrating contraption



Optional snooze balls with a special charm

Snooze ball »Smiley«:
Item no.: A-3119-0

Snooze ball »Football«:
Item no.: A-3120-0



»I am not overly grumpy in the morning. But I still like to take my time to prepare for the day. Waking up in a pleasant way is part of it.«



The »time flash« series – 1), 2):

- ◆ Powerful inbuilt flash light, directed to the front
- ◆ Silent analogue quartz movement
- ◆ Powercut backup
- ◆ Connection for vibrating pad and vibrating contraption
- ◆ Snooze function
- ◆ Toggable sound
- ◆ Clock face with automatic illumination
- ◆ Alarm on/off-display (illuminated snooze button)
- ◆ Alarm on/off switch
- ◆ Alarm tone with adjustable pitch and volume

1) lisa RF time flash

Flashing alarm clock with inbuilt lisa RF receiver

silver metallic Item no.: A-3243-0

- ◆ Alerts with strong flashes and 6 large coloured event icons. The flash can be deactivated.

2) time flash

Flashing alarm clock

silver metallic Item no.: A-3142-0

- ◆ Wakes with bright light flashes
- ◆ Toggable flash
- ◆ Phone line connection socket for indicating incoming phone calls

Telephone connection:

The »time flash« features an RJ11-socket for the parallel connection to the phone line. RJ11 connection leads and adapters are not included in the scope of delivery, but are available in every electrical specialist shop.

Specifications	HxWxD	Weight	Voltage	Cable	Power consumption
<i>lisa RF time flash</i>	95x173x57	370 g	Power supply 12 V DC		2,5 - 3,0 W
<i>time flash</i>	95x173x57	280 g	Power supply 12 V DC		2,5 - 3,0 W
Vibrating pad	30x85x85	118 g	3x AA LR6 1.5 V	connection lead 2,0 m	



▲ »lisa RF time flash set« at an advantageous price:

Item no.: A-3245-0

This set has an attractive price and consists of the lisa receiver alarm clock »lisa RF time flash« is equipped with the alerting system function, flash, loud alarm sound and the vibrating pad is included.

**Compatible accessories
for HUMANTECHNIK alerting
systems**

The supplementary vibrating pads and vibrating contraption (see back page) can also be connected to almost all alarm clocks in the HUMANTECHNIK range, to the »iBell2« mobile phone indicator and also the following alerting system components:

»lisa RF«:

Alarmo, tabletop-flashlamp, plug-in receiver, tabletop-flash-lamp connect, blinking lamp, vibrating pager

»lisa-signolux«:

Receiver T, Receiver T Connect, Receiver S, vibrating pager



»Convenient: My receiver alarm clock brings the messages of my alerting system directly to my bed.«

Flashing and vibrating alarm clocks as life savers:

Find out more about the smoke detector sets in our »lisa-signolux« and »lisa RF« alerting system portfolio.





»Sure, I have time enough. But I like to use it to get around – and not to sleep in.«



Holiday. Is someone knocking on the room or cabin door?
Does the alarm clock ring?
Does an alarm sound?
The »Traveler Set« makes calls and signals unmissable!

Please obtain detailed information from your specialist retailer and/or the HUMANTECHNIK brochure »lisa-signolux · Traveler Set«

Even in small luggage the HUMANTECHNIK alarm clocks find their space – be it the compact travel companion **travel-Tim**, the Bluetooth vibrating pad or the **VC-10** with its included vibrating pad.

1) Vibrating alarm clock VC-10

This well affordable travel companion finds its place in any luggage.

white Item no.: A-3135-0



The HUMANTECHNIK **VC-10** travel alarm clock wakes with strong vibration impulses from the connected vibrating pad. The alarm tone can be switched on and is kept **at a normal volume** so as not to disturb neighbours during hotel stays.

- ◆ Analogue quartz movement
- ◆ Separate adjusters for time and alarm
- ◆ Wakes with strong vibrations from the pad and with regular-volume alarm tone
- ◆ Non-ticking second hand
- ◆ Snooze function

- ◆ Alarm tone can be deactivated, enabling vibration-only waking
- ◆ Delivery includes a powerful vibrating pad, battery operated with 3 AA LR6 batteries (included). Battery life span: In normal operation at least 6 months
- ◆ Vibrating contraption can be connected (see accessories on back page).

Technische Daten	HxWxD (mm)	Weight	Battery	Alarm duration	Remarks
VC-10	85x120x50	170 g	1x AA LR6 1.5 V	40 min.	normal alarm volume
travelTim	95x70x30	130 g	2x AA LR6 1.5 V and 1x AAA LR3 1.5 V	4 min.	
Triple-Bel	70x45x20	68 g	2x AAA 1.5 V		
Vibrating pad	30x85x85	118 g	3x AA LR6 1.5 V		connection lead 2 m
SmartShaker 3	Ø: 99 / H: 34 mm	174 g	inbuilt rechargeable batt.		rechargeable via USB-C

»The portable alarm clocks give me free movement.
My friends and I use them at home and when travelling.
The »travelTim« is our favourite! «



2) Triple-Bel

The pocket-sized vibrating timer with visual indicator. Standing up or discreetly wearable with a clip - the ideal reminder for the kitchen, laboratory, timed medical intake and other short-term alerts.

silver

Item no.: A-3004-0

- ◆ Small size - can be discreetly fixed to your clothing
- ◆ Vibration, sound or visual signalling
- ◆ Signalarten und Zeiteinheiten ein-/ausschaltbar bzw. wählbar
- ◆ Selectable signal type
- ◆ Countdown timing, onto seconds
- ◆ Stopwatch function

3) travelTim

the modern compact travel alarm clock with its fresh design will remind you with strong vibration that it is time to get up.

black / light green Item no.: A-3020-0

black / magenta Item no.: A-3020-M

- ◆ Electronic digital clock, independent from the electrical network (AAA Battery)
- ◆ Strong inbuilt vibration
- ◆ Selectable vibration and sound, additional LED indicator
- ◆ Illuminated 24 hour display
- ◆ The protective cover serves as a stand
- ◆ Connector for additional vibrating pad or vibrating contraption (see back page).

4) SmartShaker 3

Bluetooth vibrating pad, wireless control by smartphone app.

schwarz

Item no.: A-3351-0

The »SmartShaker 3« is a stand-alone vibrating pad whose wake-up times can be programmed via a smartphone app:

- ◆ The app is available for the operating systems Android and iOS, in the respective app stores
- ◆ Simple pairing with Bluetooth 5.2
- ◆ Five different vibration settings to choose from
- ◆ Long battery life
- ◆ The programmed alarm times are activated independently of the connection to the smartphone
- ◆ If the Bluetooth connection remains active on the smartphone, the SmartShaker 3 will also report incoming calls and messages (selectable).

▲ SmartShaker 3: Alerting with powerful, adjustable vibrations.

The »SmartShaker 3« model will be replaced in the medium term by a new model called »shake:up« (A-3355-0).



»Alarm clock plus accessories - this gives me all the possibilities to find my very own favourite waking method.«



1) Vibrating pad*

black Item no.: A-3303-0

- ◆ Can be attached to all Humantechnik alarm clocks, except triple-Bel
- ◆ Place vibrating pad between bedside and mattress
- ◆ Self-supply through 3 pcs. AA (LR6) batteries, included - therefore independent from the mains electric power.
- ◆ Low batteries are indicated by a flashing LED and an altered vibration pattern

2) Vibrating contraption

- ◆ Powerful construction, will awake you from deepest sleep
- ◆ For **direct** connection to all currently available HUMANTECHNIK alarm clocks, except triple-Bel
- ◆ Sturdy fixation with 8 brackets, suitable for any standard slatted frame or spring frame
- ◆ The very strong vibration is transmitted directly to the bed frame when its time to wake up.

Model A* (2a)

Item no.: A-3310-0

For **direct** operation with alarm clocks from HUMANTECHNIK.

Item no.: A-3311-0

Model B (2b)

For operation with commercially available time switches.

Specifications	HxWxD mm	Weight	Battery / Voltage	Power consumption/ Power-cut backup	Cable
Vibrating pad	30x85x85	118 g	3x AA LR6 1.5 V	23 W	connection lead 2,0 m
Vibrating contraption A	52x74x165	1220 g	230 V	Power line 1,8 m	connection lead 1,9 m
Vibrating contraption B	52x74x165	1220 g	230 V	Power line 1,8 m	

* All alerting modules can also be connected to the following alerting system receivers: »RF lisa«: Alarmo, tabletop-flashlamp, plug-in receiver, tabletop-flashlamp connect, blinking lamp, vibrating pager / »lisa-signalux«: Receiver T, Receiver T Connect, Receiver S, vibrating pager / »iBell2«



HUMANTECHNIK

HUMANTECHNIK GmbH

Im Woerth 25 · D-79576 Weil am Rhein
Telephone: +49 (0) 76 21 / 9 56 89 - 0
Fax: +49 (0) 76 21 / 9 56 89 - 70
Internet: www.humantechnik.com
E-Mail: info@humantechnik.com

Consult your authorised dealer for comprehensive and competent advice.